

HQ-MEDIMIX MOBILE





With this mobile cart you are very flexible, the mobile dosing system can be used everywhere. The 60 liter tank with <u>sloping bottom</u> is specially designed to prevent wastage and residue of medication and/or liquids in your tank. For easy cleaning and emptying of the tank, there is a handy drain at the bottom of the tank. The trolley is made entirely of stainless steel material.

All HQ-Easymix and HQ-Solomix dosing pumps can be mounted on our mobile trolley.

Characteristics:

12V motor

Barrel 60 litre capacity

Stainless steel mixer & suction pipe

Drain for cleaning and emptying

Acid- and wear-resistant parts

All models of dosing pumps can be connected

Can be used anywhere by means of quick connectors

Trolley, mixer and barrel also available separately

 Timer switch, allows the mixer to be switched off after a certain time

Art.no. HQ-MEDIMIX	DESCRIPTION
140015	HQ-Medimix mobile: cart, 60ltr barrel, mixer and timer without pump
140016	HQ-Medimix fixed model: 60ltr barrel, mixer and timer without pump, without cart

Art.no. HQ-EASYMIX MOBILE	DESCRIPTION	Connection	BAR Max.	Dosing %
140001 (140015+140231)	HQ-Easymix mobile complete with pump	Dn20 3/4"	8	0.001-1%
140002 (140015+140232)	HQ-Easymix mobile complete with pump and auto air vent	Dn20 3/4"	8	0.001-1%
140003 (140015+140233)	HQ-Easymix mobile complete with pump	Dn20 3/4"	5	0.01-2.5%
140004 (140015+140234)	HQ-Easymix mobile complete with pump and solenoid valve	Dn20 3/4"	8	0.001-1%
Art. no. HQ-SOLOMIX MOBILE		Connection	BAR Max.	Dosing %
140005 (140015+140050)	HQ-Solomix mobile complete with pump	Dn20 3/4"	3	0.01-9.99%



Waterschoot HQ-Line BV | Groenstraat 18/B | 2450 Meerhout | BELGIUM | T.+32-14-308431 | info@hq-line.be | www.hq-line.be