

HO-MIII TIMIX





The HQ-MULTIMIX is an extremely reliable, compact, widely usable and user-friendly electronic dosage pump. Two pumps in one device working together or independently from each another.

- 1 or 2 products can be dosed simultaneously in different %
- Dosage from 0.01% up to 9.99% (standard pump)
- Dosage from 0.001% to to 1% (mini pump)
- High capacity up to 3600 ltr/h at 1% 100% accurate dosage starting from a verylow consumption (from 100cc/min.)
- Suitable for dosage of acids, medicines, peroxides etc.
- Usable for wet feeding systems
- Registration of water consumption
- Registration of product consumption
- Alarm at: watercrack, overflow, no flow
- Easy to program
- Dosage adjustable at high temperature (option)
- Combination of standard and mini pump possible
- A. Injection point
- B. Reedcontact on watermeter, pump connection
- C. Suction tube
- D. Air outlet
- "MIX" products

SAMPLE	DOSAGE

DOSAGE	LITRE PER HOUR (consumption)
0,1%	4500**
0,2%	4500**
0,5%	3600
1%	1800
2%	900
3%	600
4%	450
5%	360

(**with different	watermeter up	to 9000	Itr/hour)
-------------------	---------------	---------	-----------

% DOSAGE	DOSAGE	APPLICABLE FOR
1% - 2%	1-2ltr per 100ltr	Medicines
0,1% - 0,2%	1-2ltr per 1000ltr	Acidify
0,01% - 0,02%	1-2ltr per 10.000ltr	Disinfection

140055	HQ-Multimix 2 standard pumps
140065	HQ-Multimix 1 standard pump + 1 mini pump
140075	HQ-Multimix 2 mini pumps

The pump is supplied with watermeters and tubing depending of the pump model





WATER TREATMENT - DOSING TECHNIQUE - WATERMETERS

HQ-Line, clear in water solutions

HQ-SOLOMIX / MULTIMIX

















Dosage - Medication - Disinfection - Acidification



WATERSCHOOT HQ-Line BVBA - Groenstraat 18 /B - 2450 Meerhout - België

Tel.: +32-14-308431 info@hq-line.be Fax.: +32-14-848630 www.hq-line.be





The pump is supplied complete with watermeter and tubing

The HQ-Solomix is our base dosagepump. By means of newest technologies we can offer an extremely reliable, compact, widely usable and user-friendly dosagepump.

For a faster and better installation the watermeter and the injection point have been separated from the dosagepump. This makes it possible to assamble them on both horizontal or vertical way. On this way you will be able to install the dosagepump without getting condens on it.

Suitable for all organic acids without pre-solution and all water-soluble medication

- A. Injection point
- B. Reedcontact on watermeter, pump connection
- C Suction tube
- D Air out tubing
- E. Air outlet



The pump is supplied complete with watermeter and tubing

140005 HQ-Solomix Mini incl.1 watermeter

HQ-Solomix MINI is specially designed for *extremely low doses* for applications such as water disinfection and acidification of water.

The pump is made ??of high quality plastic materials. This makes it possible to pump almost all kinds of products; *pure and undiluted* without a pre-solution is necessary.

Gassing products such as waterstofperoxides, chlorine etc. can be used without difficulty thanks to the standard automatic air vent.

We can guarantee a long life with minimum maintenance due to the minimum presence of moving parts in the pump.

The minimum dose is standard 10cc/1000 Itr water, 0.001% (0.0001% free option) adjustable in steps of 0.001%.

HQ-Solomix MINI has a high capacity, you can easily handle your entire company with a device, the pump can also work up to 5 bar. The water meter can be adjusted to your water pipe diameter, on this way you keep enough water pressure on your company.

Sample dosage:

DOSING	cc/m³	MAX. FLOW TO ANIMALS
0.001%	10	500 m³/hour
0.010%	100	50 m³/hour
0.100%	1000	5 m³/hour
1.000%	10000	0.5 m³/hour

FEATURES AND TECHNICAL INFORMATION:		
- Operates from a very low flow (100cc / min.) - Day counter for water registration		registration
- High-precision dosing	allation, space saving - Low-maintenance plant on - Clear readable dosage	
- Compact installation, space saving		
- Easy installation		
- Injection point to mount vertically or horizontally		
	HQ-SOLOMIX	HQ-SOLOMIX MINI
- Increase / decrease in steps of	0,01%	0,001%
- Wide dosing range	0.01% t/m 9,99%	0.001% t/m 1%
- Up to pressure	3 bar	5 bar

HQ-SOLOMIX MOBILE

The electronic dosage pump Solomix has been assambled on a mobile trolley. On this stainless steel trolley, has been assambled a barrel of 50Ltr including mixer, timer and tubing.

Everywhere and rapidly usable!

* Trolley and mixer with barrel also separately available

140010	HQ-Solomix mobiel compl.
140015	HQ-Medimix Mobiel zonder pomp
140016	HQ-Medimix vast model vat en mixer